



# ZEISS Biogon T\* 2/35 M42-I



## Features

- f/2 aperture
- Moderate wide-angle lens
- Precise manual focusing
- Robust full-metal construction
- Fixation for focus and aperture
- Outstanding image quality
- Compact and lightweight
- For industrial cameras up to sensor sizes of 24x36 mm or 43mm line sensors.

### **M42-I: Industrial Edition**

Features special screws to fix focus and aperture settings even in rough situations.


### **Camera Mount**

Available with M42-Mount.



# ZEISS Biogon T\* 2/35 M42-I

## Technical Specifications




<b>Focal length</b>	35 mm
<b>Aperture range</b>	f/2 – f/22 (1/ 3 stop intervals)
<b>Number of elements / groups</b>	9 / 6
<b>Focusing range</b>	0.7 m - ∞
<b>Min. free working distance</b>	630 mm (2.07 ft.)
<b>Angular field* (diag. / horiz. / vert.)</b>	63 / 54 / 38°
<b>Max. diameter of image field</b>	43 mm (1.7")
<b>Flange focal distance</b>	M42-I: 26.8 mm
<b>Coverage at close range*</b>	43 x 65 cm
<b>Image ratio at close range</b>	1:18
<b>Filter-thread</b>	M 43 x 0.75
<b>Weight</b>	240 g (0.53 lbs)
<b>Length</b>	56 mm
<b>Camera mount</b>	M42-I

\* referring to 24x36mm sensor format



# ZEISS Biogon T\* 2/35 M42-I


## Relative Illuminance\*



The relative illumination shows the decrease in image brightness from the image center to the edge in percent.

— f-number 2.0  
... f-number 4.0

## Relative Distortion\*



The relative distortion shows the deviation of the actual image height from the ideal one in percent.


\* data for infinite focus setting



# ZEISS Biogon T\* 2/35 M42-I

## MTF Charts\*


MTF [%] k=2.0



The Modulation Transfer (MTF) as a function of image height (u) and slit orientation (sagittal, tangential) has been measured with white light at spatial frequencies of R = 10, 20 and 40 cycles/mm. The MTF charts are valid for the ZM-version and for white light.

f-number 2.0  
— Sagittal  
... Tangential

MTF [%] k=4.0



f-number 4.0  
— Sagittal  
... Tangential

\* data for infinite focus setting